

# LED Filament Bulbs



R2M2-A15



R2M2-A16/A60C



R2M2-A19/A60N



R2M2-G64



R2M2-T45



R2M2-BR30/BR95C



R2M2-BR30/BR95F



R2M2-C32



R2M2-C10-C30 Candle



R2M2-C35 Candle



R2M2-D125S



R2M2-G16



R2M2-G50



R2M2-G25/G80C



R2M2-G25/G80S



R2M2-G25/G80RG



R2M2-G25/G80S



R2M2-D30/D95D



R2M2-G30/G95L



R2M2-G40/G125G



R2M2-G40/G125L



R2M2-G40/G125



R2M2-G40C



R2M2-G150 E26



R2M2-G150



R2M2-G58G



R2M2-S14C



R2M2-ST40C



R2M2-ST64G



R2M2-ST64C



R2M2-ST64S  
R2M2-ST64SC



R2M2-ST64L



R2M2-T30N2



R2M2-T30N4



R2M2-T30N6



R2M2-T20C



R2M2-T30C2



R2M2-T30C6



R2M2-T30-185



R2M2-T30C4



R2M2-T30L8



R2M2-T30L8



R2M2-T30-300I  
2 LEDs



R2M2-T30L4



R2M2-T30L6



R2M2-T30-300L6



R2M2-T45S  
R2M2-T45C



R2M2-ST64F



R2M2-A19/A60F



R2M2-G25/G80F

Item No	Dimensions	Power	Cap Base	Finish	Lumens	Input Voltage	Light Color
R2M2-A19/A60N	Φ2.36 x 4.33"	2W,4W,6W	E26/E27/B22	Neodymium	110lm/W	AC 110V-240V	2200K-6000K
R2M2-A19/A60C	Φ2.36 x 4.33"	2W,4W,6W	E26/E27/B22	Clear	110lm/W	AC 110V-240V	2200K-6000K
R2M2-C32	Φ1.26 x 3.74"	2W,4W	E12(S)/E14(S)	Clear	110lm/W	AC 110V-240V	2200K-6000K
R2M2-C35 Candle	Φ1.38 x 4.09"	2W,4W	E12(S)/E14(S)	Clear	110lm/W	AC 110V-240V	2200K-6000K
R2M2-A15C	Φ1.89 x 3.23"	6W,8W	E26/E27/B22	Clear	110lm/W	AC 110V-240V	2200K-6000K
R2M2-A15C	Φ1.89 x 3.46"	2W,4W	E12(S)/E14(S)	Clear	110lm/W	AC 110V-240V	2200K-6000K
R2M2-A15M	Φ1.89 x 3.23"	6W,8W	E26/E27/B22	Milky	110lm/W	AC 110V-240V	2200K-6000K
R2M2-A19/A60C	Φ2.36 x 4.33"	4W,6W,8W	E26/E27/B22	Clear	110lm/W	AC 110V-240V	2200K-6000K
R2M2-A19/A60M	Φ2.36 x 4.33"	4W,6W,8W	E26/E27/B22	Milky	110lm/W	AC 110V-240V	2200K-6000K
R2M2-C35W	Φ1.38 x 3.74"	2W,4W	E12(S)/E14(S)/ E17	Clear	110lm/W	AC 110V-240V	2200K-6000K
R2M2-C35M	Φ1.38 x 3.54"	2W,4W,6W	E26/E27/B22	Milky	110lm/W	AC 110V-240V	2200K-6000K
R2M2-BR30/BR95C	Φ3.74 x 4.96"	8W	E26/E27/B22	Clear	110lm/W	AC 110V-240V	2200K-6000K
R2M2-BR30/BR95F	Φ3.74 x 4.96"	8W	E26/E27/B22	Frosted Inside + Silver Plating	110lm/W	AC 110V-240V	2200K-6000K
R2M2-D30/D95	Φ3.74 x 5.20"	4W,6W,8W	E26/E27/B22	Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
R2M2-G40C	Φ1.57 x 2.36"	1W	E12	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
R2M2-G25/G80	Φ3.15 x 7.87"	4W,6W,8W	E26/E27/B22	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K

<b>R2M2-G16</b>	Φ1.97 x 2.83"	2W,4W	E12(S)/E14(S)	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-G50</b>	Φ1.97 x 2.83"	2W,4W	E26/E27	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-G30/G95</b>	Φ6.57 x 5.20"	4W,6W,8W	E26/E27/B22	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-G25/G80RG</b>	Φ3.15 x 4.72"	4W,6W,8W	E26/E27/B22	Rose Gold Plated	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-G25/G80S</b>	Φ3.15 x 4.72"	4W,6W,8W	E26/E27/B22	Silver Plated	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-G25/G80M</b>	Φ3.15 x 4.72"	4W,6W,8W	E26/E27/B22	Milky	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-G40/G125L</b>	Φ4.92 x 6.61"	6W,8W	E26/E27/B22	Long Filament/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-G40/G125</b>	Φ4.92 x 6.61"	6W,8W	E26/E27/B22	Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-G150</b>	Φ5.91 x 9.06"	8W,12W	E26/E27/B22	Clear	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-ST64C</b>	Φ2.52 x 5.63"	3W,4W,6W,8W	E26/E27/B22	Clear	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-ST64G</b>	Φ2.52 x 5.63"	3W,4W,6W,8W	E26/E27/B22	Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-ST64S</b>	Φ2.52 x 5.63"	3W,4W,6W,8W	E26/E27/B22	Spiral Filament	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-ST64L</b>	Φ2.52 x 5.63"	3W,4W,6W,8W	E26/E27/B22	Long Filament	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-G58G</b>	Φ2.28 x 5.20"	3W,4W,6W	E26/E27/B22	Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-S14</b>	Φ1.77 x 3.35"	2W,4W	E26/E27	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-ST40C</b>	Φ1.57 x 3.74"	3W,4W,6W	E17	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-A15</b>	Φ1.89 x 3.46"	2W,4W	E12(S)/E14(S)	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T20</b>	Φ.79 x 2.28"	2W,4W	E17	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T45</b>	Φ1.77 x 4.33"	4W,6W,8W	E26/E27/B22	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T45S</b>	Φ1.77 x 4.33"	4W,6W,8W	E26/E27/B22	Spiral Filament	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30N2</b>	Φ1.18 x 5.31"	2W	E26/E27/B22	Neodymium	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30N4</b>	Φ1.18 x 5.31"	4W	E26/E27/B22	Neodymium	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30N6</b>	Φ1.18 x 5.31"	6W	E26/E27/B22	Neodymium	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30C2</b>	Φ1.18 x 7.28"	2W	E26/E27/B22	Clear	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30C4</b>	Φ1.18 x 7.28"	4W	E26/E27/B22	Clear	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30C6</b>	Φ1.18 x 7.28"	6W	E26/E27/B22	Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30M6</b>	Φ1.18 x 7.28"	6W	E26/E27/B22	Milky	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30L4</b>	Φ1.18 x 11.81"	4W	E26/E27/B22	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30L4</b>	Φ1.18 x 11.81"	4W	E26/E27/B22	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30L6</b>	Φ1.18 x 11.81"	6W	E26/E27/B22	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30L6</b>	Φ1.18 x 11.81"	6W	E26/E27/B22	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30L8</b>	Φ1.18 x 11.81"	8W	E26/E27/B22	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30L8</b>	Φ1.18 x 11.81"	8W	E26/E27/B22	Clear/Gold Tint	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-A19/A60F</b>	Φ2.36 x 4.33"	2W	E26/E27/B22	Clear	60lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-ST64F</b>	Φ2.52 x 5.63"	2W	E26/E27/B22	Clear	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-G25/G80F</b>	Φ3.15 x 4.72"	2W	E26/E27/B22	Clear	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-G30/G95F</b>	Φ3.74 x 5.20"	2W	E26/E27/B22	Clear	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T30F</b>	Φ1.18 x 7.28"	2W	E26/E27/B22	Clear	110lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-A19/A60C</b>	Φ2.36 x 4.33"	2W,4W	E26/E27/B22	Clear/Gold	60lm/W	AC 110V-240V	2200K-6000K

				Tint			
<b>R2M2-ST64SC</b>	Φ2.52 x 5.63"	2W,4W	E26/E27/B22	Clear/Gold Tint	60lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-T45SC</b>	Φ1.77 x 5.03"	2W,4W	E26/E27/B22	Spiral Filament Clear/Gold Tint	60lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-G25/G80S</b>	Φ3.15 x 4.72"	2W,4W	E26/E27/B22	Spiral Filament Clear /Gold Tint	60lm/W	AC 110V-240V	2200K-6000K
<b>R2M2-D125S</b>	Φ4.92 x 7.01"	4W	E26/E27/B22	Spiral Filament Gold Tint	60lm/W	AC 110V-240V	2200K-6000K

\*Neodymium glass filters out yellow light, resulting in a whiter light that is similar to the bluish color of daylight.